


# Micro Piezo Actuators



Obtaining an integratable, compatible, low cost mechanical energy source providing a sufficient quantity of easily accessible energy within a miniaturised system has been an ongoing challenge for decades. The urgency and interests of such systems will continue to increase with the development of portable microsystems. The conventional approach to mechanical actuation is based on electromagnetic machines. This option is very efficient but difficult to integrate at microscopic scales. Actuation making use of piezo-electric elements became widespread starting from the 1990s, and this is an important step forward for microsystems since it is very easy to integrate, it is relatively powerful and easy to use. Obviously there is still a real actuator need to be satisfied for integrated and high power actuation. Today the trend which is the extreme system miniaturisation and complexification leads to new technological and material challenges.

## Objective

In the frame of the MUFLY FP6 EC project, which targets a 20g micro-helicopter, new miniature piezo actuators and driving electronic of less than 0.2g are required. In that regard, ultra-light weight actuators with a high power to mass ratio have been developed. In addition a miniature driver for piezo-electric actuators addresses the issues of compact micro embedded components.




Fig. 1: APA® FEM Deformed structure.

## Description

These new miniature actuators are based on the concept of the standard Amplified Piezo Actuators. The APA® utilises the metallic shell to amplified motions from the piezo stack and to pre-stress it (Fig.1). This pre-stress is required to withstand large external vibrations.

### Micro Amplified Piezo Actuator: APA $\mu$ XS

The APA  $\mu$ XS (Fig.2) is the smallest actuator of the range of CEDRAT TECHNOLOGIES' APA®. Since they are based on tiny MLA, special care was provided in the design. They offer the following features:

- Ultra light weight,
- Small and Compact,
- Great Stroke,
- High bandwidth,
- Robust design,
- Low cost.



Fig. 2: View of the APA  $\mu$ XS.

### Micro Tilt: Tilt $\mu$ XS

The new micro tilt (Fig.3) of CEDRAT TECHNOLOGIES, so called Tilt  $\mu$ XS, is based on two APA  $\mu$ XS's and a level arm realised in a monolithic part. Thickness, hinge Length and the pivot point pitch are optimised to allow the maximum deflection amplification on the arm tip. Indeed, the level of stroke amplification in relation to the APA  $\mu$ XS is up to 6.





Fig. 3: View of the Tilt  $\mu$ XS.

# Micro Piezo Actuators



## Micro Double Tilt Translator: DTT $\mu$ XS

Using the same approach of amplification, a three level of amplification device, so called DTT  $\mu$ XS (Fig.4), has been developed. It is based on four Tilts  $\mu$ XS's: The stroke of the two pairs of APA<sup>®</sup> are amplified angularly around a pivot point to produce a large stroke around Rx, Ry and Tz.




Fig.4: CAD View of the DTT  $\mu$ XS.

## Miniature Driver For Piezo-electric Actuators: CA $\mu$ 10

The piezo-electric driver CA $\mu$ 10 (Fig.5) consists in a small Printed Circuit Board and dedicated connections with the piezoelectric actuators. It includes the following main electronic functions:

- A DC/DC converter,
- A linear amplifier able to magnify an input analogue order,
- A SPI digital to analogue converter able to convert 12 bits words in analogue signal for the linear amplifier. Optional inputs can be connected if necessary to shunt the SPI bus and send directly the analogue order on the linear amplifiers.




Fig.5: View of the CA $\mu$ 10.

## Performance

Typical performances are given in the following table. This table is not exhaustive as many other actuators can be designed by CEDRAT TECHNOLOGIES using its design tools, lab facilities and technological know-how.

References	Unit	APA $\mu$ XS	Tilt $\mu$ XS	DTT $\mu$ XS
Notes		Preliminary	Preliminary	Preliminary
Linear Stroke	$\mu$ m	60	320	320
Angular Stroke	$^{\circ}$	N.A	N.A	10 $^{\circ}$
Blocked Force	N	1,4	1	4
Voltage	V	0-150	0-150	0-150
Maximal frequency Blocked-Free	Hz	3500	800	N.A
Stiffness	N/m	25 000	3 000	12 000
Dimension	mm	5*12*1	16*25*1	N.A
Mass	g	0,15	0,35	1,5
Electrical interface		2 wires AWG	4 wires AWG	16 wires AWG
Mechanical interface		1*1 flat square	2* M1 drilled holes	2*4 M1 drilled holes

Fig.6: Micro actuators performances.

References	Unit	CA $\mu$ 10
Notes		Preliminary
Number of channel	None	2 channels + push-pull version
Output voltage	Volts	5 to 150
Output current (a)	mA	5 per channel
Total Harmonic Distorsion(b)	%	0,2
Signal to noise ratio (c)	dB	70
Output load	$\mu$ F	0.025 to 40
Amplifier quiescent current	$\mu$ A	900 per channel
Gain (d)	V/V	45
Order Input range	V	2.7 to 5.5
Bandwidth (e)	Hz	min 450
Converter efficiency (f)	%	80
Input voltage	DC Volts	3.3 to 15.5
Maximum average input power (g)	W	up to 1,5W
Maximum peak input power (h)	W	up to 3W
Mechanical interfaces	None	4 holes diameter 1.6mm
Electrical interfaces	None	Power input lines, actuator output lines and command lines (analogue or via SPI link) With solder pads
Dimensions	mm	19.5 x 23 x 7
Weight	grams	2,2

Fig.7: CA $\mu$ 10 performances.

For more information, please contact:

CEDRAT TECHNOLOGIES  
 15 Chemin de Malacher - Inovallée  
 38246 Meylan Cedex - France  
[actuator@cedrat.com](mailto:actuator@cedrat.com)  
 Phone: +33 (0)4 76 90 50 45 - Fax: +33 (0)4 56 38 08 30